

WANTED

For **IMMEDIATE TURN-IN**

MILSTD Generators



DO NOT USE or KEEP FOR BACKUP

**Send to DLA Disposition Services
Requisition Replacement TQG ASAP!**

**Email the Old MILSTD Generator's LIN and NIIN to the
Following Item Manager and Request Replacement:**

Miriam Travers miriam.b.travers.civ@mail.mil

**NOTE: New TQGs can be shipped immediately if units take old
stock off their property book BEFORE requesting replacement.**



New NSN, Class for 65 GPM Water Pump

Get a new 65 gallon-per-minute (GPM) water pump with NSN 4320-01-507-0595. It replaces NSNs 4320-00-752-9466, 4320-00-542-3346, 4320-01-276-0573 and 4320-01-338-8010, which are obsolete. This new pump also transitioned from a Class VII major item to a Class II secondary item. All unserviceable pumps under NSNs 4320-00-752-9466, 4320-00-542-3346, 4320-01-276-0573 and 4320-01-338-8010 should be turned in to DLA Disposition Services.

Mending MOLLE

Fix tears less than an inch long in your modular lightweight load-carrying equipment (MOLLE) hydration system's carrier with cloth tape, NSN 8315-00-958-0744. If fabric is ripped no more than three inches, sew it with the needle and thread from the tentage repair kit, NSN 8340-00-262-5767. For longer tears, you may need to replace the carrier.